



PR No. 1000036868

Rfx No. 6100001594

**Technical Specification**  
**Add-on Components for Up-gradation of Existing Rock Triaxial System**

Upgradation of the existing rock triaxial test facility, the following components are sought.

- 1. High-pressure platens for specimen diameter 38mm Comprising which has to be added to existing High-pressure Triaxial cell (2 inches, 70 MPa) to enable triaxial and permeability tests on 38mm sample size including:**
  - a) Hardened upper endcap with pore pressure port. Made of hardened steel (stress of 600MPa)
  - b) Hardened Lower platen with pore pressure port. Made of hardened steel (maximum stress of 600MPa)
  - c) Set of seals(O-rings) for sealing jacket to platens
  - d) Load piston and base adapter with connecting ports for pore pressure and permeability tests
  - e) One Rubber tubing of 38 mm diameter (for installation and training purposes)
  - f) Dummy specimen made of Stainless Steel (One number)
  - g) All items must have an Operational temperature: Up to a maximum operational temperature of 100C degrees and an operational Confining pressure rating: Up to maximum cell pressure of 70Mpa
  - h) Software upgrading for calculation of all parameters for 38mm sample size
  
- 2. High-pressure platens for specimen diameter 25.4 mm comprising which has to be added to existing High-pressure Triaxial cell (2 inches, 70 Mpa) to enable triaxial and permeability tests on 25.4 mm sample size including of:**
  - a) Hardened upper endcap with pore pressure port. Made of hardened steel (stress of 600MPa)
  - b) Hardened Lower platen with pore pressure port. Made of hardened steel(maximum stress of 600MPa)
  - c) Set of seals(O-rings) for sealing jacket to platens



INDIAN INSTITUTE OF TECHNOLOGY BOMBAY  
MATERIALS MANAGEMENT DIVISION  
Powai, Mumbai - 400076

- d) Load piston and base adapter with connecting ports for pore pressure and permeability tests
- e) One Rubber tubing for 25.4 mm diameter (for installation and training purpose)
- f) Dummy specimen made of Stainless Steel (One number)
- g) All items must have an Operational temperature: Up to a maximum operational temperature of 100°C degrees and operational Confining pressure rating: Up to maximum cell pressure of 70 MPa
- h) Software upgrading for calculation of all parameters for 25.4 mm sample size

**3. Advanced compact ultrasonic transmission system for measurements of P- and S-wave velocities up to 1 MHz to be adapted with existing triaxial test device (70 MPa)**

- a) Including amplifier and data acquisition system and software for ultrasonic velocity measurement with the facility of waveform stacking, filtering, and power spectra analysis.
- b) Set of non-corrosive adapter platens for Sample diameter of 38 mm and 50.8 mm for ultrasonic P & S wave measurements for HP-HT cell (working condition 70 MPa-100°C degree) Comprising of Hardened upper and lower endcaps, Set of seals, Connecting ports for pore pressure
- c) Set of non-corrosive adapter platens for Sample diameter of 25.4 mm and 47.6 mm for ultrasonic P & S wave measurements for HP-HT cell (working condition 70 MPa-100°C degree) Comprising of Hardened upper and lower endcaps, Set of seals, Connecting ports for pore pressure
- d) High-pressure feed-throughs for existing Triaxial cell and the above-mentioned items

**4. Upgrading of current triaxial cell in the laboratory for running triaxial tests under temperature control up to 100-degree C including all required components e.g., Ceramic isolation between the load piston, actuator, cell base and frame, Temperature sensor, High-pressure feed-throughs, Isolation package and temperature control software module which has to be integrated into current software of the device**



**5. High accuracy Single Syringe pump, Table top version for Gas permeability tests appropriate to pass n.c. CO<sub>2</sub>, N<sub>2</sub>, CH<sub>4</sub> and Air**

- a) Max. pressure range: 70 MPa
- b) Pressure resolution: 0.02 bar
- c) Pressure accuracy: 0.1% F.S
- d) Volume: 290 ml
- e) Flow accuracy: 0.0002 ml/min
- f) Software module for permeability test to be integrated into the current software of the device.
- g) Required accessories to be connected to Triaxial cell, for example, pressure lines, valves, etc.

**6. Warranty 18 months**